

# Zehntner Industrial Parts Catalog

## Axiparts Global Industrial RFQ Platform

Email: [info@axiparts.com](mailto:info@axiparts.com)

Website: <https://axiparts.com>

Premium RFQ catalog for Zehntner industrial spare parts, MRO components and replacement products. Every listed product is linked directly to its live RFQ product page.

**Brand:** Zehntner

**Listed Products in This PDF:** 80

**Catalog URL:** <https://axiparts.com/catalogs/brands/zehntner.pdf>

Part Number	Product Description	Live RFQ Link
1120.268	1120.268	<a href="#">Open Product RFQ Page</a>
2055.25	2055.25 ZNW 2055 Zehntner-Nassfilm-Prüfkamm-Rad	<a href="#">Open Product RFQ Page</a>
2087.1	2087.1	<a href="#">Open Product RFQ Page</a>
2087.15	2087.15	<a href="#">Open Product RFQ Page</a>
2087.2	2087.2	<a href="#">Open Product RFQ Page</a>
2087.3	2087.3	<a href="#">Open Product RFQ Page</a>
2087.4	2087.4	<a href="#">Open Product RFQ Page</a>
2087.5	2087.5	<a href="#">Open Product RFQ Page</a>
2087.6	2087.6	<a href="#">Open Product RFQ Page</a>
2160.1	2160.1	<a href="#">Open Product RFQ Page</a>
2160.2	2160.2	<a href="#">Open Product RFQ Page</a>
2160.3	2160.3	<a href="#">Open Product RFQ Page</a>
5800	5800 (SRT 5800 PENDELGERÄT) (1 tragbares Griffigkeitsmessgerät mit höhenverstellbarem Gestell mit Pendelarm und Skala 5 lange Gleitkörper nach Ihrer W	<a href="#">Open Product RFQ Page</a>
6013+	6013+ ZRM 6013+ Zehntner-Retroreflektometer RL/Qd	<a href="#">Open Product RFQ Page</a>
6060.ASTM	6060.ASTM ZRS 6060 Zehntner-Retroreflektometer	<a href="#">Open Product RFQ Page</a>
6060.CD	6060.CD ZRS 6060 Zehntner-Retroreflektometer	<a href="#">Open Product RFQ Page</a>
6060.CEN	6060.CEN ZRS 6060 Zehntner-Retroreflektometer	<a href="#">Open Product RFQ Page</a>
6060.DE	6060.DE	<a href="#">Open Product RFQ Page</a>
6060.EN	6060.EN ZRS 6060 Zehntner-Retroreflektometer	<a href="#">Open Product RFQ Page</a>
ACC036	ACC036 Spare lamp RL	<a href="#">Open Product RFQ Page</a>
ACC037	ACC037 Spare lamp (Qd)	<a href="#">Open Product RFQ Page</a>
ACC112	ACC112	<a href="#">Open Product RFQ Page</a>
ACC378.004	ACC378.004 Profile rod ACC378.004 Profile rod with wet film thickness 4.57 µm (0.18 mil)	<a href="#">Open Product RFQ Page</a>

Part Number	Product Description	Live RFQ Link
ACC378.006	ACC378.006 Profile rod ACC378.006 Profile rod with wet film thickness 6.86 µm (0.27 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.009	ACC378.009 Profile rod ACC378.009 Profile rod with wet film thickness 9.14 µm (0.36 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.011	ACC378.011 Profile rod ACC378.011 Profile rod with wet film thickness 11.43 µm (0.45 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.013	ACC378.013 Profile rod ACC378.013 Profile rod with wet film thickness 13.72 µm (0.54 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.016	ACC378.016 Profile rod ACC378.016 Profile rod with wet film thickness 16.00 µm (0.63 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.018	ACC378.018 Profile rod ACC378.018 Profile rod with wet film thickness 18.29 µm (0.72 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.020	ACC378.020 Profile rod ACC378.020 Profile rod with wet film thickness 20.57 µm (0.81 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.022	ACC378.022 Profile rod ACC378.022 Profile rod with wet film thickness 22.86 µm (0.90 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.027	ACC378.027 Profile rod ACC378.027 Profile rod with wet film thickness 27.43 µm (1.08 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.032	ACC378.032 Profile rod ACC378.032 Profile rod with wet film thickness 32.00 µm (1.26 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.036	ACC378.036 Profile rod ACC378.036 Profile rod with wet film thickness 36.58 µm (1.44 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.041	ACC378.041 Profile rod ACC378.041 Profile rod with wet film thickness 41.15 µm (1.62 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.045	ACC378.045 Profile rod ACC378.045 Profile rod with wet film thickness 45.72 µm (1.80 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.050	ACC378.050 Profile rod ACC378.050 Profile rod with wet film thickness 50.29 µm (1.98 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.054	ACC378.054 Profile rod ACC378.054 Profile rod with wet film thickness 54.86 µm (2.16 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.059	ACC378.059 Profile rod ACC378.059 Profile rod with wet film thickness 59.44 µm (2.34 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.064	ACC378.064 Profile rod ACC378.064 Profile rod with wet film thickness 64.01 µm (2.52 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.068	ACC378.068 Profile rod ACC378.068 Profile rod with wet film thickness 68.58 µm (2.70 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.073	ACC378.073 Profile rod ACC378.073 Profile rod with wet film thickness 73.15 µm (2.88 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.077	ACC378.077 Profile rod ACC378.077 Profile rod with wet film thickness 77.72 µm (3.06 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.082	ACC378.082 Profile rod ACC378.082 Profile rod with wet film thickness 82.30 µm (3.24 mil)	<a href="#">Open Product RFQ Page</a>
ACC378.086	ACC378.086 Profile rod ACC378.086 Profile rod with wet film thickness 86.87 µm (3.42 mil)	<a href="#">Open Product RFQ Page</a>

Part Number	Product Description	Live RFQ Link
ACC378.091	ACC378.091 Profile rod ACC378.091 Profile rod with wet film thickness 91.44 µm (3.60 mil)	Open Product RFQ Page
ACC378.096	ACC378.096 Profile rod ACC378.096 Profile rod with wet film thickness 96.01 µm (3.78 mil)	Open Product RFQ Page
ACC378.100	ACC378.100 Profile rod ACC378.100 Profile rod with wet film thickness 100.58 µm (3.96 mil)	Open Product RFQ Page
ACC378.105	ACC378.105 Profile rod ACC378.105 Profile rod with wet film thickness 105.16 µm (4.14 mil)	Open Product RFQ Page
ACC378.109	ACC378.109 Profile rod ACC378.109 Profile rod with wet film thickness 109.73 µm (4.32 mil)	Open Product RFQ Page
ACC378.114	ACC378.114 Profile rod ACC378.114 Profile rod with wet film thickness 114.30 µm (4.50 mil)	Open Product RFQ Page
ACC378.125	ACC378.125 Profile rod ACC378.125 Profile rod with wet film thickness 125.73 µm (4.95 mil)	Open Product RFQ Page
ACC378.137	ACC378.137 Profile rod ACC378.137 Profile rod with wet film thickness 137.16 µm (5.40 mil)	Open Product RFQ Page
ACC378.148	ACC378.148 Profile rod ACC378.148 Profile rod with wet film thickness 148.59 µm (5.85 mil)	Open Product RFQ Page
ACC378.160	ACC378.160 Profile rod ACC378.160 Profile rod with wet film thickness 160.02 µm (6.30 mil)	Open Product RFQ Page
ACC378.171	ACC378.171 Profile rod ACC378.171 Profile rod with wet film thickness 171.45 µm (6.75 mil)	Open Product RFQ Page
ACC378.S	ACC378.S Profile rod ACC378.S Profile rod with wet film thickness on request	Open Product RFQ Page
ACC593	ACC593 - optional	Open Product RFQ Page
GL-920601	GL-920601 MINI-MICROGLOSSMETER	Open Product RFQ Page
GL-921303	GL-921303 MINI-MICRO	Open Product RFQ Page
PA-930149,	PA-930149, ZSF 2196 S SCRATCHING TOOL WITH 1mm BLADE TO SIKKENS	Open Product RFQ Page
P/N:	P/N: 6014 Type: ZRM 6014 Retroreflectometer	Open Product RFQ Page
S/N:10101310	S/N:10101310 TYPE:ZRM 1013+ obsolete, alternatives ZRM 6014 or ZRM 6013+	Open Product RFQ Page
ZCC	ZCC 2080 Cross-cut Tester	Open Product RFQ Page
ZCF	ZCF 2088 Cross-cut Tester	Open Product RFQ Page
ZCT	ZCT 2160 Cross-cut Templet	Open Product RFQ Page
ZDR	ZDR 6020.EU.1m Dynamic Retroreflectometer RL	Open Product RFQ Page
ZFC	ZFC 3012 Zehntner-Tauchauslaufbecher	Open Product RFQ Page
ZGH	ZGH 1024.6 glosshaze and gloss 60° (dual angle)	Open Product RFQ Page
ZGM	ZGM 1130.	Open Product RFQ Page
ZHC	ZHC 1200 HELMEN®-Chalking tester	Open Product RFQ Page

Part Number	Product Description	Live RFQ Link
ZHT-2093	ZHT-2093 pocket hardness testers	<a href="#">Open Product RFQ Page</a>
ZMM	ZMM 5000.mm ZMM 5000 Digital Marking Gauge with display in mm	<a href="#">Open Product RFQ Page</a>
ZND	ZND 2053	<a href="#">Open Product RFQ Page</a>
ZRM	ZRM 6006	<a href="#">Open Product RFQ Page</a>
ZRS	ZRS 6060[6060.C.S.02.033.1]	<a href="#">Open Product RFQ Page</a>
ZSF	ZSF 2196	<a href="#">Open Product RFQ Page</a>
ZVL	ZVL 2190	<a href="#">Open Product RFQ Page</a>
ZWW	ZWW 2100	<a href="#">Open Product RFQ Page</a>
ZZS	ZZS 1110	<a href="#">Open Product RFQ Page</a>

### Axiparts Offices

Germany Head Office: Lise-Meitner-Straße 13, 89081 Ulm, Germany

USA Office: 16225 Park Ten Pl #500, Houston, TX 77084, United States

Dubai Office: HDS Business Centre Tower, Cluster M, 33rd Floor, Jumeirah Lake Towers, Dubai, United Arab Emirates